

## STUKO HKC

## Characteristics

Appearance	: White Thick Paste
Base	: Expandable Microspheres
Solid Content	: $27 \pm 1\%$
pH (10% Sol.)	: $9.0 \pm 0.5$
Viscosity	: 40000-50000 CPS
Lightfastness	: Excellent

*Stucco and priming agent based on pre-expanded microspheres, used on corrected grain or heavy damaged grain leathers to cover imperfections and upgrade leather selection.*

STUKO HKC is "wax free", colloidal filler containing pre-expanded polymeric microspheres dispersed in modified polyurethane resin dispersions. The product is in paste form - used as sealer coat and mender putty for filling defects and up gradation of leather. It exhibits excellent filling properties, print retention and very effective coverage of grain defects.

STUKO HKC, due to its aliphatic PU base, exhibits excellent lightfastness, cold-crack, flex endurance, water resistance and prepares the surface well for subsequent finishing operations. Treated leathers are hair cell plated and snuffed before proceeding further for finishing, thus effectively filling/hiding the surface defects of leather.

Usage

Apply Stuko HKC with spatula on defected parts of grain to fill up, dry properly, leave for 10-12 hours. Plate at 90°C and snuff. Proceed with the normal finishing

## REACH COMPLIANT



## Green-Trek- Compliant

A symbol of our commitment to sustainable technologies

Storage : Store between +5 'c to 35 'c in original pack, well-sealed & stored.  
Shelf-life : Product is stable for 6 months from the date of production / Invoice.



Non flammable

Avoid direct contact with skin



Prevent from freezing

Use Gloves / Ensure Ventilation



Note: Suggested formulations are only for guidance and necessary modifications must be made to achieve a particular result.